

icountPD



icountPD User Manual



P849139, Issue 3

© Parker Hannifin, 2008

www.parker.com/hfde

Laser Information

This product contains an invisible infrared 5mW laser.

Any dismantling of the product may result in dangerous exposure to laser radiation.



DANGER

INVISIBLE LASER RADIATION
WHEN OPEN. AVOID DIRECT
EXPOSURE TO BEAM.

Note: Users are not required to access the laser radiation source and should never do so.

EC Declaration of Conformity

EC Declaration of Conformity

Document No. DoC0001-issue 3



Parker Hannifin (UK) Ltd
Hydraulic Filter Division Europe
Condition Monitoring Centre
Brunel Way, Thetford, Norfolk
IP24 1HP, United Kingdom

Product(s):

The following icountPD products have been approved:

- *icountPD compatible with mineral, aggressive oils and aviation fuels*
- *icountPD calibrated with ACFTD and MTD*
- *icountPD with or without a display (LED or digital)*
- *icountPD with or without a limit relay*
- *icountPD with RS232, 4-20mA, 0-3/0-5V and CANBUS (J1939) outputs*
- *icountPD with or without a Mositure Sensor*
- *icountPD fitted with the fixed 5 metre cable, Deutsch connector or M12 connector.*

The Product(s) described above are in conformity with the essential requirements of the following directives:

89/336/EEC amended by 92/31/EEC, 93/68/EEC and repealed by 2004/108/EEC

Harmonised standards:

EN61000-6-3:2001 *Electromagnetic compatibility – Part 6-3: Generic standards – Emission standard for residential, commercial and light-industrial environments.*
EN61000-6-2:2001 *Electromagnetic compatibility (EMC) – Part 6-2: Generic standards – Immunity for industrial environments*

Signed for and on behalf of Parker Hannifin (UK) Ltd, Thetford
13th May 2008

Steve Newcomb
Operations Manager

CMC E12 Issue 1, May 07

Contents

Laser Information.....	2
EC Declaration of Conformity.....	2
Introduction.....	4
Principles of operation	4
Benefits.....	5
Technical specification	6
Product software default settings.....	7
Product features.....	8
Dimensions for installation	8
Connections.....	9
Hydraulic connection.....	9
Flow control.....	9
System 20 sensor connection	10
Electrical connection.....	11
4–20mA output settings	16
Variable voltage output settings.....	17
CAN-bus network output option	17
Moisture sensor output settings	17
Digital Display Unit connection	18
RS232 connectivity.....	20
Software	21
icountPD Setup Utility software	21
Microsoft Windows® HyperTerminal connection	24
Communication protocol	26
Front panel displays.....	30
LED display parameters (ISO4406 / NAS1638)	30
Digital display parameters (ISO 4406 / NAS 1638).....	31
Reference	34
Optional wiring configuration.....	34
Optional Limit Relay Hysteresis	34
Interpreting data.....	36
ISO/NAS/SAE comparison chart	40
Component cleanliness guidelines	41
Viscosity charts.....	42
ISO contamination charts.....	43
Ordering Information.....	45

Introduction

Parker Hannifin's icountPD represents the most up-to-date technology in solid particle contamination analysis. The icountPD is a compact, permanently-mounted laser-based particle detector module that provides a cost-effective solution to fluid management and contamination control.

Principles of operation

The icountPD measures particle contamination continuously and updates the display, output options and limit relay every second.


Unlike the Parker CM20, LCM20 or MCM20, the unit does not perform a 'one-off' test. This means that even if the Measurement Period is set to 60 seconds, the display, output and limit relay all report the presence of dirt in the oil in just a few seconds – it does not wait until the end of the Measurement Period before reporting the result.

The icountPD has just one setting to control the accuracy, stability and sensitivity of the measurements and that is the 'Measurement Period'. This can be set from 5 seconds to 180 seconds. The longer the Measurement Period, the more contaminant is measured, averaging out any spikes seen on a smaller sample. The shorter the Measurement Period the more sensitive the icountPD is to small slugs of contaminant, but also the performance on clean systems can be reduced. Thus, the user can select how sensitive the icountPD is to spikes of contaminant, and how quickly it responds to contamination levels above the set point ('limits').

With a Measurement Period of 100 seconds, the results will be for the last 100ml of oil that has flowed through the icountPD, updated on a second-by-second basis, giving an effectively continuous readout of the level of contamination.

Safety requirements

Refer to the Parker Hannifin Quality and Servicing booklet (FDCB272UK), supplied on CD.



Maintenance requirements

Ensure that the power supply is disconnected before any maintenance/inspection is carried out. Please contact Parker Hannifin in the unlikely event of the icountPD being faulty or damaged.

Calibration recommendations

Contact your local Parker Hannifin Sales Company for recalibration. The recommended recalibration frequency is 12 months.

Storage requirements

Store in dry conditions within a temperature range of -20°C to +40°C (-4°F to +104°F).

Benefits

- Independent monitoring of system contamination trends
- Calibration by recognised online principles confirmed by relevant International Organization for Standardization (ISO) procedures
- Early warning LED or digital display indicators for Low, Medium and High contamination levels
- A low cost solution to prolonging fluid life and reducing machine downtime
- Visual indicators with power and alarm output warnings
- Self-diagnostic software
- Mineral and phosphate ester fluid compatible construction – see the ‘Product Configurator’, page 45, for fluid type options
- Fully PC/PLC integration technology such as: RS232, 0–5V, 4–20mA and CAN-bus (SAE J1939) – see the ‘Product Configurator’, page 45, for communication options
- Percentage saturation reporting through an integrated moisture sensor – see the ‘Product Configurator’, page 45, for moisture sensor options.

Technical specification


Feature	Specification
Product start-up time	5 seconds minimum
Measurement period	5–180 seconds
Reporting interval	0–3600 seconds via RS232 communication
Principle of operation	Laser Diode optical detection of actual particulates
International codes	ISO 7 – 22, NAS 0 – 12
Calibration	By recognised online methods confirmed by the relevant ISO procedures. MTD – Via a certified primary ISO 11171 automatic particle detector using ISO 11943 principles, with particle distribution reporting to ISO 4406:1996 ACFTD – Conforming to ISO 4402 principles with particle distribution reporting to ISO 4406:1996
Recalibration	Contact Parker Hannifin
Working pressure	2–420 bar (30–6000 PSI)
Flow range through icountPD	Note: Flow may be bi-directional 40–140 ml/min (optimum flow 60 ml/min) (0.01 – 0.04 USGPM (optimum flow 0.016 USGPM))
Online flow range via System 20 sensors	Size 0 = 6 to 25 l/min (2–7 USGPM) Size 1 = 24 to 100 l/min (6–26 USGPM) Size 2 = 170 to 380 l/min (45–100 USGPM)
Ambient storage temperature	–20°C to +40°C (–4°F to +104°F)
Environment operating temperature	+5°C to +60°C (+41°F to 140°F)
Fluid operating temperature	+5°C to +80°C (+41°F to 176°F)
Computer compatibility	Parker recommends the use of a 9-way D-type connector. This can be connected to a USB port using a USB-serial adaptor. Note that these connectors/adaptors are NOT supplied with icountPD units: contact Parker Hannifin for advice.
Moisture sensor calibration	±5% RH (over compensated temperature range of +10°C to +80°C; +50°F to +176°F)
Operating humidity range	5% RH to 100% RH
Moisture sensor stability	±0.2% RH typical at 50% RH in one year
Power requirement	Regulated 9–40Vdc
Current rating	Typically 120mA
Certification	IP66 rating Refer to the EC Declaration of Conformity (page 2).
Analogue output options (specified when ordering)	
Variable current	4–20mA
Variable voltage	0–5Vdc, 0–3Vdc (user selectable)
CAN-bus	to SAE J1939 (e.g. <i>Parker IQAN</i>)
Moisture sensor	Linear scale within the range 5% RH to 100% RH

Product software default settings

Standard defaults	
Comms echo	OFF
Verbose errors	OFF
STI Sensors used	OFF
Reporting standards	ISO
Particle limits	19 / 18 / 15
Measurement period	60 seconds
Reporting interval	30 seconds
Power-on mode	AUTO
Auto start delay	5 seconds
Date format	dd/mm/yy


Default if options fitted	
Relay hysteresis	ON
Relay operation for particle limits	ON
Relay operation for moisture sensor limits	ON
Digital display orientation	0 degrees
Digital display brightness level	3-mid
0–5V/0–3V output voltage range	0–5V
Moisture sensor limit	70%

Product features



Dimensions for installation

Dimensions are given in mm (inches)



Connections

Hydraulic connection



Our recommendation is to position the icountPD as close to the system output as possible whilst controlling the flow to the optimum 60ml/min. This then provides the highest pressure conditions, plus the oil in this position is indicative of the reservoir's oil condition.

For transportation, the icountPD is supplied with two test point covers: these need to be removed.

The mineral oil version of icountPD is supplied with M16 x 2 hydraulic test points. Parker recommends that these are **not removed or loosened**. If these test points are not required please contact Parker Hannifin for alternative options.

Note that the phosphate ester oil version of the icountPD is supplied with 5/8 inch BSF hydraulic test points.

For Hydraulic connection:

1. Connect two pressure hoses to either end of the icountPD test points.
2. Connect the opposite end of the pressure hoses to the application.

Note: The connection of these test points should be 'finger tight' only. Do not use spanners or wrenches.

Flow control

A pressure compensated, flow control device (Parker Hannifin part number S840074) has been developed to give the icountPD user greater flexibility. The flow control device enables testing where flow ranges are outside the icountPD specifications (i.e. 40–140 ml/min), or where pipe diameters do not allow the icountPD to be installed.

Required Differential Pressure Range 5–315 Bar

The flow control device fits onto the downstream (outlet) side of the icountPD, connecting through a manifold block via a self-sealing quick connection test point.

The differential pressure valve automatically compensates for pressure and viscosity changes, whilst maintaining its flow setting even as the workload changes.

The table below is used to select the appropriate valve position:

Valve position	cSt range
3	20–100
3.8	90–200
4.2	190–320
5	310–500



System 20 sensor connection

Online flow range via System 20 inline sensors:


Size 0	6 to 25 l/min (optimum flow = 15 l/min)
Size 1	24 to 100 l/min (optimum flow = 70 l/min)
Size 2	170 to 380 l/min (optimum flow = 250 l/min)

The required differential pressure across inline sensors is 0.4 bar (minimum)


Refer to the 'Sensor part numbers' section on page 46 before ordering System 20 sensors.

See 'Inline Sensor Monitors' (Parker Hannifin Brochure CM013GB1) for more information on System 20 sensors.


Size 0 Sensor



Size 1 Sensor



Size 2 Sensor



(All dimensions are in millimetres)

IMPORTANT NOTE: P1 and P2 of the System 20 sensors **MUST** be connected to the icountPD test points. Ensure that the icountPD command 'SSU' is set to 'Yes' when connecting to icountPD – refer to 'Communication protocol' section of this manual for a list of user commands.

Contact Parker Hannifin if you require further advice in connecting icountPD to your system.

Electrical connection



Supply and Limit relay

5 metre (16 ft) cable, *or*
M12, 8-pin plug cable (150mm (6 inch)
flying lead), *or*
DT series Deutsch receptacle connector
(150mm (6 inch) flying lead).

Communication cable

5 metre (16 ft) communication cable,
or
M12, 8-pin socket communication
cable (150mm (6 inch) flying lead), *or*
DT series Deutsch plug connector
cable (150mm (6 inch) flying lead).

5 metre communication cable: electrical connection

Wire colour	No options fitted	4–20mA option fitted	0–5V/0–3V option fitted
Red	Product supply 9–40Vdc	Product supply 9–40Vdc	Product supply 9–40Vdc
Black	Product supply 0Vdc	Product supply 0Vdc	Product supply 0Vdc
Green	NOT USED	Channel A ISO 4µm (c)	Channel A ISO 4µm (c)
Yellow	NOT USED	Channel B ISO 6µm (c) <i>or</i> NAS (if selected)	Channel B ISO 6µm (c) <i>or</i> NAS (if selected)
White	NOT USED	Channel C ISO 14µm (c)	Channel C ISO 14µm (c)
Blue	NOT USED	Moisture sensor channel (if fitted)	Moisture sensor channel (if fitted)
Brown	NOT USED	4–20mA Supply 12–20Vdc	0–5V / 0–3V Supply 12–24Vdc
Violet (purple)	NOT USED	NOT USED	0–5V / 0–3V Supply 0 Vdc
Orange	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)
Grey	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)
Pink	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)
Turquoise (cyan)	NOT USED	NOT USED	NOT USED

Note: If the moisture sensor is fitted without either 4–20mA or 0–5V/0–3V option then the output is via RS232.


** Note: Parker recommends the use of a 9-way, D-type socket for use with RS232 with the stated pin configuration*

IMPORTANT NOTE: It is the responsibility of the end user to ensure that the cable's braided screen is terminated to a suitable earth bonding point.

5 metre limit relay cable (optional): electrical connection

Wire colour	Standard
Red	Normally open
Blue	Normally closed
White	Common

M12 Communication cable: electrical connection



Pin configuration diagram


M12 female connector, end view

Pin number (Wire colour recommended)	No options fitted	4–20mA option fitted	0–5V/0–3V option fitted
1 (White)	NOT USED	Channel C, ISO 14µm(c)	Channel C, ISO 14µm(c)
2 (Brown)	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)
3 (Green)	NOT USED	Channel A, ISO 4µm(c)	Channel A, ISO 4µm(c)
4 (Yellow)	NOT USED	Channel B, ISO 6µm(c) or NAS (if selected)	Channel B, ISO 6µm(c) or NAS (if selected)
5 (Grey)	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)
6 (Pink)	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)
7 (Blue)	NOT USED	Moisture sensor channel (if fitted)	Moisture sensor channel (if fitted)
8 (Red)	NOT USED	NOT USED	NOT USED

Note: If the moisture sensor is fitted without the 4–20mA or the 0–5V/0–3V option, then the output is via RS232.

** Parker recommends the use of a 9-way D-type socket with RS232, using the pin configurations given in the above table.*

M12 Supply and Limit relay cable (if fitted): electrical connection




Pin configuration diagram
M12 male connector, end view

Pin number (Wire colour recommended)	No options fitted	4–20mA option fitted	0–5V/0–3V option fitted
1 (White)	Relay Normally Closed (if fitted)	Relay Normally Closed (if fitted)	Relay Normally Closed (if fitted)
2 (Brown)	NOT USED	4–20mA Supply 12–20Vdc	0–5 / 0–3V Supply 12–24Vdc
3 (Green)	Relay Common (if fitted)	Relay Common (if fitted)	Relay Common (if fitted)
4 (Yellow)	Relay Normally Open (if fitted)	Relay Normally Open (if fitted)	Relay Normally Open (if fitted)
5 (Grey)	NOT USED	NOT USED	NOT USED
6 (Pink)	NOT USED	NOT USED	0–5V / 0–3V Supply 0 Vdc
7 (Blue)	Product supply 0Vdc	Product supply 0Vdc	Product supply 0Vdc
8 (Red)	Product supply 9–40Vdc	Product supply 9–40Vdc	Product supply 9–40Vdc

Parker Hannifin recommend that the mating M12 connector cables are screened. These cables are available from Parker Hannifin – see ‘Accessory part numbers’ on page 45 of this manual.

IMPORTANT NOTE: *It is the responsibility of the end user to ensure that the cable's braided screen is terminated to a suitable earth bonding point.*

Deutsch Communication cable: electrical connection




Pin configuration diagram
Deutsch female connector, end view

Pin number	No options fitted	4–20mA option fitted	0–5V/0–3V option fitted	CAN option fitted
1	NOT USED	Channel C, ISO 14μm(c)	Channel C, ISO 14μm(c)	NOT USED
2	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)	RS232 Ground (* Pin 5)
3	NOT USED	Channel A, ISO 4μm(c)	Channel A, ISO 4μm(c)	CAN+
4	NOT USED	Channel B, ISO 6μm(c) or NAS (if selected)	Channel B, ISO 6μm(c) or NAS (if selected)	CAN–
5	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)	RS232 Receive (* Pin 3)
6	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)	RS232 Transmit (* Pin 2)
7	NOT USED	Moisture sensor channel (if fitted)	Moisture sensor channel (if fitted)	CAN Ground
8	NOT USED	NOT USED	NOT USED	NOT USED
9	NOT USED	NOT USED	NOT USED	NOT USED
10	NOT USED	NOT USED	NOT USED	NOT USED
11	NOT USED	NOT USED	NOT USED	NOT USED
12	Screen termination	Screen termination	Screen termination	Screen termination

Note: If the moisture sensor is fitted without the 4–20mA or the 0–5V/0–3V option, then the output is via RS232.

** Parker recommends the use of a 9-way D-type socket with RS232, using the pin configurations given in the above table.*

Deutsch Supply and Relay cable (if fitted): electrical connection



Pin configuration diagram
Deutsch male connector, end view

Pin number	No options fitted	4–20mA option fitted	0–5V/0–3V option fitted	CAN option fitted
1	Relay Normally Closed (if fitted)	Relay Normally Closed (if fitted)	Relay Normally Closed (if fitted)	NOT USED
2	NOT USED	4–20mA Supply 12–20Vdc	0–5V / 0–3V Supply 12–24Vdc	NOT USED
3	Relay Common (if fitted)	Relay Common (if fitted)	Relay Common (if fitted)	NOT USED
4	Relay Normally Open (if fitted)	Relay Normally Open (if fitted)	Relay Normally Open (if fitted)	NOT USED
5	NOT USED	NOT USED	NOT USED	NOT USED
6	NOT USED	NOT USED	0–5V / 0–3V supply 0Vdc	NOT USED
7	Product supply 0Vdc	Product supply 0Vdc	Product supply 0Vdc	Product supply 0Vdc
8	Product supply 9–40Vdc	Product supply 9–40Vdc	Product supply 9–40Vdc	Product supply 9–40Vdc
9	NOT USED	NOT USED	NOT USED	NOT USED
10	NOT USED	NOT USED	NOT USED	NOT USED
11	NOT USED	NOT USED	NOT USED	NOT USED
12	Screen termination	Screen termination	Screen termination	NOT USED

Parker Hannifin recommend that the mating Deutsch connector cables are screened. These cables are available from Parker Hannifin – see the ‘icountPD part number specifier’ section in this manual.

IMPORTANT NOTE: *It is the responsibility of the end user to ensure that the cable's braided screen is terminated to a suitable earth bonding point.*

4–20mA output settings

The following table can be used to relate the analogue output to an ISO or NAS code. For example, ISO code 12 is equal to an output of 10mA.


mA	4.0	4.5	5.0	5.5	6.0	6.5	7.0	7.5	8.0	8.5	9.0	9.5	10.0	10.5	11.0	11.5	12.0
ISO	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16

mA cont...	12.5	13.0	13.5	14.0	14.5	15.0	15.5	16.0	16.5	17.0	17.5	18.0	18.5	19.0	19.5	20
ISO cont...	17	18	19	20	21	22	*	*	*	*	*	*	*	Over-range		ERROR

mA	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
NAS	00	0	1	2	3	4	5	6	7	8	9	10	11	12	*	*	ERROR

Note: * = Saturation (Above ISO code 22 and NAS code 12)

ISO setting




The actual calculation is as follows:

mA current = (ISO code / 2) + 4
e.g. 10mA = (ISO 12 / 2) + 4

or

ISO code = (mA current - 4) x 2
e.g. ISO 12 = (10mA - 4) x 2

NAS setting



The actual calculation is as follows:

mA current = NAS code + 5
e.g. 15mA = NAS 10 + 5

or

NAS code = mA current - 5
e.g. NAS 10 = 15mA - 5

Variable voltage output settings

The variable voltage output option is capable of two different voltage ranges: a 0–5Vdc range as standard, and a user-selectable 0–3Vdc range. The ‘Full list of commands’ section of this manual (page 27-29) gives information on how to change the voltage output.

The following tables can be used to relate the analogue output to an ISO or NAS code.

For example, in a 0–5Vdc range, ISO code 16 is equal to an output of 3.5Vdc. In a 0–3Vdc range, ISO code 8 is equal to an output of 1.0Vdc.

Table relating ISO codes to Voltage output

ISO	Err	0	1	2	3	4	5	6	7	8	9	10	11
0–5Vdc	<0.2	0.3	0.5	0.7	0.9	1.1	1.3	1.5	1.7	1.9	2.1	2.3	2.5
0–3Vdc	<0.15	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0	1.1	1.2	1.3

cont.	ISO	12	13	14	15	16	17	18	19	20	21	22	Err
	0–5Vdc	2.7	2.9	3.1	3.3	3.5	3.7	3.9	4.1	4.3	4.5	4.7	>4.8
	0–3Vdc	1.4	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	>2.45

Table relating NAS codes to Voltage output

NAS	Err	00	0	1	2	3	4	5	6	7	8	9	10	11	12	Err
0–5Vdc	<0.4	0.6	0.9	1.2	1.5	1.8	2.1	2.4	2.7	3.0	3.3	3.6	3.9	4.2	4.5	>4.6
0–3Vdc	<0.2	N.S.	0.3	0.5	0.7	0.9	1.1	1.3	1.5	1.7	1.9	2.1	2.3	2.5	2.7	>2.8

(N.S. = Not Supported)

CAN-bus network output option

If you plan to use the icountPD with a CAN-bus (SAE J1939) network, you can order this output option when specifying the icountPD. Refer to the ‘Product configurator’ (page 45) in the Reference section of this manual. The CAN option provides an interface to external CAN-bus networked systems (for example, to the *Parker IQAN*).

Moisture sensor output settings


The Moisture sensor is an option that can be included when specifying the icountPD. Refer to the ‘Product configurator’ (page 45) in the Reference section of this manual.

The Moisture sensor reports on the saturation levels of the fluid passing through the icountPD sensing cell. The output is a linear scale, reporting within the range of 5% saturation to 100% saturation.

Table relating Saturation levels in the sensing cell to icountPD outputs

Saturation	4–20mA	0–3Vdc	0–5Vdc
5%	4.8	0.15	0.25
25%	8	0.75	1.25
50%	12	1.50	2.50
75%	16	2.25	3.75
100%	20	3.00	5.00


Digital Display Unit connection



The above diagram shows how Channels A, B and C, plus the Moisture Sensor (if fitted) can be wired to Parker DDUs.

Digital Display Units available

Part number	Description
DDU1001	Process indicator 22-55Vdc
DDU1002	Process indicator 90-264Vdc



The above diagram shows how a single DDU can be used to display Channels A, B and C, plus the Moisture Sensor (if fitted) by using a switch to display each channel in turn.

RS232 connectivity

Communication can be established between icountPD and a PC using an RS232 serial connection with the **Parker Utility Setup Tool**, the **Parker Terminal** utility, or via Microsoft Windows® **HyperTerminal**.

Please note that **HyperTerminal** is not supplied with Windows Vista™, but the **Parker Utility Setup Tool** and **Parker Terminal** can be used with this operating system. Both Parker programs are supplied on the icountPD CD.

PC connection

The RS232 wires need to be connected to a 9-way D-type connector (not supplied as standard). For the connector pin termination and wire colour, refer to the 'Communication cable wiring configuration' section of this manual (page 11).

The device can then be either connected direct to PC serial port (Figure 1) or connected via an RS232-to-USB adaptor cable (Figure 2).

An RS232 to USB convertor can be supplied by Parker Hannifin (part number B84011).




Figure 1





Figure 2

Note: The 9-way D-type connector, RS232-to-USB adaptor cable and installation software are not supplied as standard with the icountPD.


**STEP 2:**

Set the values for 'Detector ID' and 'Date Format'.


The remaining detector information is preset by Parker Hannifin and cannot be changed.

STEP 3:

Set the values in 'Measurement Configuration', 'Relay Options' and 'Alarm Limits'.

**STEP 4:**

Set the values for Orientation and Brightness Level in 'Display Options' and Voltage Range (0-5V, 0-3V or J1939) in 'Output Options' if either of these options are fitted.



STEP 5:

Setup values are verified as valid in 'Results'.

Click 'Start' to start verification and 'Stop' to stop.

Microsoft Windows® HyperTerminal connection

An alternative way of achieving communication with icountPD is to use the HyperTerminal program supplied with Microsoft Windows (but not always installed on the PC or laptop's hard disk – check the installation disk, or contact your organisation's IT department if the program is not present). **Please note that HyperTerminal is not supplied with Windows Vista™, but the Parker Terminal utility can be used with this operating system.**

The standard communication settings (used in STEP 4) are as follows:

Baud Rate	9600
Data bits	8
Parity	None
Stop bits	1
Flowcontrol	None



STEP 1:



Click 'Start'

STEP 2:

Select 'HyperTerminal'.

(from All Programs

- ▶ Accessories
- ▶ Communications
- ▶ HyperTerminal)



STEP 3:



Click and type the connection name you wish to use to identify this session

**STEP 4:**

Select the appropriate USB port.

STEP 5:

Enter the communication settings (as in the 'standard communications settings' table, on the previous page).

**STEP 6:**

Once the iCountPD is connected to power, the product identification is displayed. This identifies successful communication to iCountPD. The iCountPD is now ready for operation.

Communication protocol

The commands used with the icountPD are either made up of Set, Read or Start/Stop commands.

- Set commands allow the value or values of parameters to be changed
- Read commands allow the value or values of parameters to be read
- Start/Stop commands allow the user to start and stop tests.

Example:

[SDF dd/mm/yy] sets the date format

[RDF] reads the product format date

All commands are sent in ASCII characters, and the protocol accepts both upper and lower case characters. For example, all of the following codes are equivalent:

SDF = Sdf = SDf = sdf

Note: The use of a '=' after a command, for example [SDF = dd/mm/yy], is optional.

Certain commands are for internal use only and can be accessed via a password system. Should an unauthorized person attempt to access these commands the icountPD returns an error code for 'Invalid Command'.

Common commands

Common User Read commands		
Command	Description	icountPD response
RDU	Read calibration dust	Calibration dust displayed (i.e. MTD or ACFTD)
RLT	Read NAS or ISO limits	Limits displayed
RRS	Read reporting standard	ISO or NAS displayed

Common User Set commands		
Command	Description	User response
SLT	Set limits i.e. 'SLT 19 18 15'	SLT ## ## ## (for ISO) SLT ## (for NAS)
SRS	Set reporting standard	SRS iso SRS nas
SRI	Set reporting interval 0 to 3600 seconds 0 = No reporting	SRI #####

Note: The reporting interval (SRI) controls how often the icountPD sends results over the RS232.

User Start/Stop commands		
Command	Description	Response
STR or START	Start testing	'OK' displayed
STP or STOP	Stop testing	'OK' displayed

Full list of commands

User Read Commands		
Command	Description	icountPD response
RCD	Read the last C alibration D ate	Last calibration date displayed
RCE	Read C ommunication E cho	'ON' or 'OFF' displayed
	<i>Comms Echo ON allows the icountPD to communicate in two directions (Hyperterminal)</i> <i>Comms Echo OFF allows the icountPD to communicate in one direction (Setup Utility)</i>	
RDB	Read D isplay B rightness	Brightness levels 1–5
RDD	Read the next calibration D ue D ate	Next calibration due date displayed
RDF	Read D ate F ormat	Date format displayed (i.e. dd/mm/yy)
RDI	Read D etector I D	Detector ID displayed
RDO	Read Digital D isplay O rientation ⁴	RDO=0 Normal (0°), RDO=1 90° RDO=2 180°, RDO=3 270°
RDS	Read D etector S tatus	IPD status displayed (i.e. RUNNING)
RDU	Read the calibration D ust U nit	Calibration dust displayed (i.e. MTD or ACFTD)
REN	Read last E rror N umber	Last error number displayed
RER	Read last E rror text R eport	Last error text displayed
REV	Read the E rror V erbose mode	Error verbose mode displayed
	<i>Error Verbose ON displays the full description of the error code (i.e. Error 40 - expected On or Off)</i> <i>Error Verbose OFF displays just the error code (i.e. Error 40)</i>	
RFN	Read F ault N umber	Fault number displayed
RJE	Read J 1939 Status	'ON' or 'OFF' displayed
RLR	Read the L ast contamination R esult	Last contamination result displayed
RLT	Read contamination L imit T hreshold	Contamination limits displayed
RML	Read M oisture sensor L imit ¹	Moisture limit displayed
RMP	Read M easurement P eriod	Measurement period displayed
RMV	Read the last M oisture sensor V alue ¹	Last moisture result displayed
ROF	Read O ptions F itted	ROF = ABCDEFGHIJ (see list of options below)
RON	Read O ption N ame	List of options A = Alarm relay option B = LED display option C = OLED display option D = Moisture sensor option E = 4–20mA current loop option F = 0–3/0–5V option G = J1939 option H = reserved I = reserved J = reserved
RPD	Read the P ower on hold-off D elay	Power hold-off delay displayed
RPI	Read P roduct I dentifier	icountPD displayed
RPM	Read the P ower on M ode	'AUTO' or 'MANUAL' displayed

RPN	Read the icountPD Part Number	Parker part number displayed
RPT	Read Product Type	IPDH or IPDH
RPV	Read Protocol Version	Protocol version displayed
RRI	Read Reporting Interval	Reporting interval displayed
RRS	Read Reporting Standard	'ISO' or 'NAS' displayed
RSB	Read Software Build number	Software build number displayed
RSH	Read limit relay Switch Hysteresis ²	'ON' or 'OFF' displayed
RSL	Read Standards List	ISO, NAS
RSN	Read Serial Number	Serial number displayed
RSS	Read limit relay Switch State ²	'ON' or 'OFF' displayed
RSU	Read STI Sensor Used	'YES' or 'NO' displayed
RSV	Read Software Version displayed	Software version displayed
RVM	Read the Voltage Maximum range ³	Voltage range displayed
RWC	Read Warning limit relay for Contamination ²	'ON' or 'OFF' displayed
RWM	Read Warning limit relay for Moisture _{1,2}	'ON' or 'OFF' displayed

¹ Command requires a Moisture Sensor to be fitted to icountPD

² Command requires a Limit Relay to be fitted to icountPD

³ Command requires a 0–5V option to be fitted to icountPD

⁴ Command requires digital display option to be fitted to icountPD

User Set Commands		
Command	Description	icountPD response
SCE	Set Communication Echo	SCE on SCE off
	<i>Comms Echo ON allows icountPD to communicate in two directions (Hyperterminal) Comms Echo OFF allows icountPD to communicate in one direction (Setup Utility)</i>	
SDB	Set Display Brightness	Set levels 1–5
SDF	Set Date Format	SDF dd/mm/yy SDF mm/dd/yy SDF yy/mm/dd
SDI	Set Detector ID	SDI ##### (14 characters maximum, spaces not allowed)
SDO	Set Digital Display Orientation ⁴	SDO=0 Normal (0°), SDO=1 90° SDO=2 180°, SDO=3 270°
SEV	Set the Error Verbose mode	SEV on SEV off
	<i>Error Verbose ON displays the full description of the error code (i.e. Error 40 - Expected On or Off) Error Verbose OFF displays just the error code (i.e. Error 40)</i>	
SJE	Set J1939 Status	SJE On/Off (can only set On)

SLT	S et c ontamination L imit T hreshold	SLT ## ## ## (for ISO) SLT ## (for NAS)
SML	S et M oisture sensor L imit ¹	SML ###
SMP	S et M easurement P eriod	SMP ### (### = 5 to 180 seconds)
	<i>The Measurement period sets the number of seconds the detector uses to determine the contamination levels. So if this is 60 seconds, the unit will use the last 60 seconds of oil to determine the contamination level. (See the 'Component cleanliness guideline' chart in the Reference section of this manual.)</i>	
SPD	S et the P ower on hold-off D elay	SPD ### (### = 0 to 900 seconds)
	<i>The Power-on hold-off delay command allows the user to delay the start of the icountPD operation.</i>	
SPM	S et the P ower on M ode	SPM auto SPM manual
	<i>With the Power-on Mode set to 'Auto' icountPD starts testing automatically when the power is connected using the last setup parameters. With the Power-on Mode set to 'Manual' icountPD becomes idle and requires the user to manually start testing.</i>	
SRI	S et R eporting I nterval	SRI mm:ss (0 to 3600 seconds (i.e. 0–1 hour); note that 0 = No reporting)
	<i>The Reporting Interval controls how often icountPD sends results over the RS232</i>	
SRS	S et R eporting S tandard	SRS iso SRS nas
SSH	S et limit relay S witch H ysteresis ²	SSH on SSH off
SSS	S et limit relay S witch S tate ²	SSS on SSS off
SSU	S et STI S ensor U sed	SSU yes SSU no
SVM	S et the V oltage M aximum range ³	SVM # (3 = 0–3Vdc output 5 = 0–5Vdc output)
SWC	S et W arning limit relay for C ontamination ^{2, 5}	SWC on SWC off
SWM	S et W arning limit relay for M oisture ^{1, 2, 5}	SWM on SWM off

¹ Command requires a Moisture sensor to be fitted to the icountPD

² Command requires a Limit Relay to be fitted to the icountPD

³ Command requires a 0–5Vdc option to be fitted to the icountPD

⁴ Command requires digital display option to be fitted to icountPD

⁵ If the Limit Relay has been turned OFF for both Contamination monitoring and Moisture sensing, the Limit Relay will not operate, but the alarm status is not affected.

If the Limit Relay has been turned ON for both Contamination monitoring and Moisture sensing, the Limit Relay will operate when any alarm condition is reached.


Front panel displays

LED display parameters (ISO4406 / NAS1638)

Start up

1. Once the icountPD has been connected to a regulated power supply, all four LEDs will roll from top to bottom for a minimum of five seconds as the icountPD performs a system diagnostic check.
2. The icountPD then automatically starts monitoring using the factory default test parameters. Only if the Power on Mode is set to Auto (product default).

LED indication



The icountPD uses LED 1, 2 and 3 for the indication of ISO 4406; LED 2 alone is used for the NAS1638 code. Individual code lights trigger according to user settings. The order of triggering is:

- **Solid green** trips at all codes below the set point (limit) code.
- **Flashing green** LED trips at the set point code.
- **Solid red** LED trips at the set point plus 1 code.
- **Flashing red** LED trips at the set point plus 2 codes.

LED 4 is reserved for the icountPD Moisture Sensor. Contact Parker Hannifin for details of its specification.

ISO example

Assuming the limits on the icountPD have been set to 18/16/12 and the actual particles detected by the icountPD is giving a ISO result of 20/17/11.

- LED 1 **flashes red**, 2 codes higher than the set limit.
- LED 2 appears **solid red** (1 code higher),
- LED 3 appears **solid green** (1 code lower).

NAS example:

Assuming that the limit on the icountPD has been set to 7 and the actual particles detected by the icountPD is giving a NAS result of 9.

- LED 2 **flashes red** (2 codes higher) .

LED Moisture sensor indicator (LED 4):

- **Solid green** trips at %RH (percentage Relative Humidity) level or below the set point (limit).
- **Solid red** trips above the %RH level.

Error detection

Errors which can be easily corrected are indicated by a **short flashing amber** LED.

LED 1	LED 2	
On	Off	Fault 1 – Laser too hot – Oil is too hot. Allow to cool
Off	On	Fault 2 – Light level is bad – Flush with clean oil and retry


Errors that require the unit to be returned to the supplier or service centre are indicated by a **double flashing amber** LED.

LED 1	LED 2	
On	Off	Fault 1 – Channel failure – Impossible Count Readings

Digital display parameters (ISO 4406 / NAS 1638)

Start up

1. Once the icountPD has been connected to a regulated power supply, the product logo is displayed for approximately five seconds as the icountPD performs a system diagnostic check.
2. The icountPD then automatically starts monitoring using the factory default test parameters. Only if the Power on Mode is set to Auto (product default).



Digital display indication

The digital display shows the actual measured codes, the size per channel (in microns) and the user definable limits. Note that the channel size and the limits are displayed alternately.

If the Moisture Sensor option is fitted, the Moisture Sensor reading (%RH) is also shown.

The order of trigger for both ISO, NAS and Moisture Sensor option is:

- Solid digit(s) – code(s) that are at or below the set point (limit).
- Flashing digit(s) – code(s) that are above the set point (limit).


Automatic Light Sensor

The digital display on the icountPD is fitted with an automatic light sensor. This automatically adjusts the brightness of the display for optimal reading, depending on the actual light conditions where the product is located.

The icountPD brightness level default is 3. The brightness levels range from 1 (low) to 5 (high), 3 being the mid-point.

Display Orientation

The digital display can be orientated using the icountPD Setup Utility software to suit the way in which the unit has been fitted. The default display orientation is 0°; the other settings are 90°, 180°, and 270° clockwise from default.



Error detection

In the unlikely event of a error occurring, the normal display is completely replaced by an error code (for example, 'Error 13'). The error messages correspond to the following error code:

Code	Message
Error 0	No error
Error 1	Unknown command
Error 2	Characters after command ignored
Error 3	Command ignored – unit is busy
Error 5	Unexpected character found
Error 6	Symbol too long
Error 7	Bad command format
Error 8	Unknown value
Error 9	Invalid date format
Error 10	Invalid date
Error 13	Option not fitted
Error 14	String too short
Error 15	String too long
Error 17	No test result
Error 18	Number expected
Error 19	Number too long
Error 20	Number out of range
Error 30	Interval shorter than duration
Error 40	Expected On or Off
Error 41	Expected Disabled or Enabled
Error 43	Expected Auto or Manual
Error 45	Expected Yes or No


Reference

Optional wiring configuration

5 metre limit relay cable wiring configuration

The icountPD can be specified to include a built-in limit switch relay which can be triggered when a preset alarm level is reached. The relay contacts can be used to switch an external device on or off. Each wire within the icountPD limit relay cable is identified as **Red**, **White** and **Blue** which corresponds with the diagram below.

Wire colour	Description
Red	Normally Open
Blue	Normally Closed
White	Common



The contact rating is 5A at 5–24Vdc

IMPORTANT NOTE: It is the responsibility of the end user to ensure that the cable's braided screen is terminated.

Optional Limit Relay Hysteresis

Hysteresis is a property of systems (usually physical systems) that do not instantly follow the forces applied to them, but react slowly, or do not return completely to their original state.

To set Relay Limits, refer to the 'Communication Protocol – User Commands' section in this manual.

Hysteresis feature ON

The relay will energise when any channel is one code above the set limit (i.e. LEDs are **solid red**) and will only de-energize when all channels are one code below the set limit (i.e. All LEDs are **solid green**).

Hysteresis feature OFF

The relay will energise when any channel is one code above the set limit (i.e. LEDs are **solid red**) and will only de-energize when all channels are on the set limit (i.e. All LEDs are **flashing green**).

Example ISO scenario

An icountPD has been connected to a hydraulic fluid transfer system. With the icountPD limit relay switched off (Normally Closed), the limits set to ISO 20/18/13 and the relay cable electrically connected to a Parker 10MFP Filtration Trolley. The icountPD will activate the 10MFP as soon as the set limits are breached. The ten test results below show the effect of having the hysteresis on or off:

	Hysteresis feature ON 10MFP Trolley status		Hysteresis feature OFF 10MFP Trolley status	
Test 1 result – 20/16/13	OFF		OFF	
Test 2 result – 21/16/13		ON		ON
Test 3 result – 20/16/13		ON	OFF	
Test 4 result – 18/17/14		ON		ON
Test 5 result – 18/16/13		ON	OFF	
Test 6 result – 17/16/11		ON		ON
Test 7 result – 17/16/11	OFF		OFF	
Test 8 result – 18/17/13	OFF		OFF	
Test 9 result – 19/17/14		ON		ON
Test 10 result – 19/17/13		ON	OFF	
ON = Relay activated, OFF = Relay not activated				

Note: Electrical connection to a 10MFP Filtration Trolley requires the use of a relay


Example NAS scenario

An icountPD has been connected to a hydraulic system on a wind turbine. The icountPD limit relay is switched off (Normally Closed), the limits set to NAS 9 and the relay cable is connected to a Parker Guardian Filtration Unit. The icountPD activates the Guardian Filtration Unit as soon as the set limit is breached. The ten test results below show the effect of having the hysteresis on or off:

	Hysteresis feature ON Guardian Unit status		Hysteresis feature OFF Guardian Unit status	
Test 1 result = 9	OFF		OFF	
Test 2 result = 9	OFF		OFF	
Test 3 result = 10		ON		ON
Test 4 result = 9		ON	OFF	
Test 5 result = 10		ON		ON
Test 6 result = 8	OFF		OFF	
Test 7 result = 7	OFF		OFF	
Test 8 result = 10		ON		ON
Test 9 result = 9		ON	OFF	
Test 10 result = 10		ON		ON
ON = Relay activated, OFF = Relay not activated				

Note: Electrical connection to a Guardian Filtration unit requires the use of a relay

The first scale number represents the number of particles larger than $4\mu\text{m(c)}$ per 100 millilitre of fluid, the second number for particles larger than $6\mu\text{m(c)}$ per 100 millilitre of fluid and the third number for particles larger than $14\mu\text{m(c)}$ per 100 millilitre of fluid.



ISO contamination numbers

Range number	Number of particles per 100ml	
	More than	Up to and including
24	8×10^6	16×10^6
23	4×10^6	8×10^6
22	2×10^6	4×10^6
21	1×10^6	2×10^6
20	500×10^3	1×10^6
19	250×10^3	500×10^3
18	130×10^3	250×10^3
17	64×10^3	130×10^3
16	32×10^3	64×10^3
15	16×10^3	32×10^3
14	8×10^3	16×10^3
13	4×10^3	8×10^3
12	2×10^3	4×10^3
11	1×10^3	2×10^3
10	500	1×10^3
9	250	500
8	130	250
7	64	130
6	32	64
5	16	32
4	8	16
3	4	8
2	2	4
1	1	2

For example: code 20/18/13 indicates that there are between 500,000 and 1,000,000 particles larger than 2 microns, and between 130,000 and 250,000 particles larger than 5 microns, and between 4000 and 8000 particles larger than 15 microns.


Reference ISO 4406:1999

When the raw data in one of the size ranges results in a particle count of fewer than 20 particles, the scale number for that size range is labelled with the symbol '>'.

For example, a code of **14/12/>7** signifies that there are more than 8,000 and up to and including 16,000 particles equal to or larger than 4µm (c) per 100 ml and more than 2,000 and up to and including 4,000 particles equal to or larger than 6µm (c) per 100 ml. The third part of the code, >7 indicates that there are more than 64 and up to and including 130 particles equal to or larger than 14µm (c) per 100 ml. But the 14µm (c) part of the code could actually be 7, indicating a particle count more than 130 particles per 100 ml.

ISO4406 particle distribution chart

Including various ISO level contamination grades



NAS 1638 chart

	Size range μm	5–15	15–25	25–50	50–100	>100
Classes (based on maximum contamination limits, particles per 100ml)	00	125	22	4	1	0
	0	250	44	8	2	0
	1	500	89	16	3	1
	2	1000	178	32	6	1
	3	2000	356	63	11	2
	4	4000	712	126	22	4
	5	8000	1425	253	45	8
	6	16,000	2850	506	90	16
	7	32,000	5700	1012	180	32
	8	64,000	11,400	2025	360	64
	9	128,000	22,800	4050	720	128
	10	256,000	45,600	8100	1440	256
	11	512,000	91,000	16,200	2880	512
	12	1,024,000	182,400	32,400	5760	1024

ISO/NAS/SAE comparison chart

BS 5540/4	Defence Std. 05/42		NAS 1638	SAE 749
	Table A	Table B		
11/8			2	
12/9			3	0
13/10			4	1
14/9		400F		
14/11			5	2
15/9	400			
15/10		800F		
15/12			6	3
16/10	800			
16/11		1300F		
16/13			7	4
17/11	1300	2000		
17/14			8	5
18/12	2000			
18/13		4400F		
18/15			9	6
19/13	4400	6300F		
19/16			10	
20/13	6300			
20/17			11	
21/14	15,000			
21/18			12	
22/15	21,000			
23/17	100,000			

The above comparisons relate to particle count data only. To confirm to any particular standard, reference should be made to the recommended experimental procedure.

Component cleanliness guidelines

Suggested acceptable contamination levels for various hydraulic systems.



Target contamination class to ISO 4406		Suggested maximum particle level		Sensitivity	Type of system	Typical components
6µm	14µm	6µm	14µm			
13	9	4000	250	Super critical	Silt-sensitive control system with very high reliability. Laboratory or aerospace.	High performance servovalves
15	11	16,000	1,000	Critical	High performance servo and high pressure long life systems, e.g. aircraft, machine tools etc.	Industrial servovalves
16	13	32,000	4,000	Very important	High quality reliable systems. General machine requirements.	Piston pumps, proportional valves, compensated flow controls
18	14	130,000	8,000	Important	General machinery and mobile systems. Medium pressure, medium capacity.	Vane pumps, spool valves
19	15	250,000	16,000	Average	Low pressure heavy industrial systems, or applications where long life is not critical.	Gear pumps, manual and poppet valves, cylinders
21	17	1,000,000	64,000	Main protection	Low pressure systems with large clearances.	Ram pumps

Viscosity charts

The following charts indicate the differential pressure required to run a successful test at the appropriate flow rates.

Example: If the fluid you wish to analyse has a relative viscosity to 60 cSt, to generate the optimum flow rate 60ml/min a differential pressure of 0.5bar is required.

If the fluid you wish to analyse has a relative viscosity of 400 cSt, a 4 bar differential pressure would result in 130 ml/min.







ISO contamination charts

Typical system applications and code numbers

These typical applications and ISO code numbers are taken from the UK Contamination and Control Research Programme (1980–1984).


Ref. *AHEM Guide to Contamination Control in Hydraulic Power Systems – 1985*

Solid Contaminant Code No 13/10 Application: Aircraft test stands	Number of particles per ml greater than indicated size  particle size μm Number of particles per 100 ml greater than indicated size
Solid Contaminant Code No 18/11 Application: Mobile systems	Number of particles per ml greater than indicated size  particle size μm Number of particles per 100 ml greater than indicated size
Solid Contaminant Code No 17/12 Application: Marine installations	Number of particles per ml greater than indicated size  particle size μm Number of particles per 100 ml greater than indicated size
Solid Contaminant Code No 18/13 Applications: Mechanical handling	Number of particles per ml greater than indicated size  particle size μm Number of particles per 100 ml greater than indicated size

Solid Contaminant Code No 16/11

Applications: Injection moulding;
Metalworking;
Unused commercial-grade oil

Number of particles per ml greater than indicated size



Number of particles per 100 ml greater than indicated size

Ordering Information

Standard products table

Part Number	Fluid type	Calibration	Display	Limit Relay	Communications	Moisture sensor	Cable connector kit	Future option
IPD12211100	Mineral	MTD	LED	No	RS232	No	No	N/A
IPD12221100	Mineral	MTD	LED	Yes	RS232	No	No	N/A
IPD12212100	Mineral	MTD	LED	No	RS232/4–20mA	No	No	N/A
IPD12222100	Mineral	MTD	LED	Yes	RS232/4–20mA	No	No	N/A
IPD12311130	Mineral	MTD	Digital	No	RS232	No	M12	N/A
IPD12321130	Mineral	MTD	Digital	Yes	RS232	No	M12	N/A
IPD12312130	Mineral	MTD	Digital	No	RS232/4–20mA	No	M12	N/A
IPD12322130	Mineral	MTD	Digital	Yes	RS232/4–20mA	No	M12	N/A

Product configurator

Key	Fluid type		Calibration		Display		Limit relay		Comms		Moisture sensor		Cable connector kit		Future option
IPD	1	Mineral	1	ACFTD	1	None	1	No	1	RS232	1	No	0	No	0
	2	Phosphate ester	2	MTD	2	LED	2	Yes	2	RS232/4–20mA	2	Yes	1	Deutsch 12-pin DT series connector	
	3	Aviation fuel, hazardous area	3	AS4059	3	Digital			3	RS232/0–5V			3	M12, 8-pin plug connector	
	4	Aviation fuel, non-hazardous area			4	GSM			4	RS232/RS485					
									5	RS232/CAN-bus					

Accessory part numbers

Description	Part number	
	Mineral oil	Aggressive fluid
1 metre hose length	ACC6NN001	ACC6NN002 **
2 metre hose length	ACC6NN003	ACC6NN004 **
5 metre hose length	ACC6NN005	ACC6NN006 **
Test Point ¼ inch BSP fitting	ACC6NN007	ACC6NN008
Test Point ⅛ inch BSP fitting	ACC6NN009	ACC6NN010
Test Point ⅛ inch NPT fitting	ACC6NN011	ACC6NN012
Single Point Sampler	SPS2021	SPS2061
External flow device	S840074	Contact Parker
Power supply	ACC6NN013	
5 metre M12, 8-pin plug and socket cable kit *	ACC6NN014	ACC6NN015
Deutsch 12-pin connector kit	ACC6NN016	
RS232 to USB converter	ACC6NN017	

* The M12 cable kit consists of two 5 metre cables (a communications cable and a relay/power supply cable) that enable all output options.

** Note that the Aggressive fluid hoses are provided as a single hose, not in pairs.

Sensor part numbers

Product number	Supersedes	Size	Flow range (l/min)	Fluid type	Port thread (inches)
STI0144100	STI.0144.100	0	6–25	Mineral oil	$\frac{3}{8}$
STI1144100	STI.1144.100	1	20–100	Mineral oil	$\frac{3}{4}$
STI2144100	STI.2144.100	2	80–380	Mineral oil	1 $\frac{1}{4}$
STI0148100	STI.0148.100	0	6–25	Aggressive fluid	$\frac{3}{8}$
STI1148100	STI.1148.100	1	20–100	Aggressive fluid	$\frac{3}{4}$
STI2148100	STI.2148.100	2	80–380	Aggressive fluid	1 $\frac{1}{4}$

Parker Worldwide

AE – UAE, Dubai
Tel: +971 4 8875600
parker.me@parker.com

AR – Argentina, Buenos Aires
Tel: +54 3327 44 4129

AT – Austria, Wiener Neustadt
Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt
Tel: +43 (0)2622 23501 970
parker.easteurope@parker.com

AU – Australia, Castle Hill
Tel: +61 (0)2-9634 7777

AZ – Azerbaijan, Baku
Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles
Tel: +32 (0)67 280 900
parker.belgium@parker.com

BR – Brazil, Cachoeirinha RS
Tel: +55 51 3470 9144

BY – Belarus, Minsk
Tel: +375 17 209 9399
parker.belarus@parker.com

CA – Canada, Milton, Ontario
Tel: +1 905 693 3000

CH – Switzerland, Etoy
Tel: +41 (0) 21 821 02 30
parker.switzerland@parker.com

CN – China, Shanghai
Tel: +86 21 5031 2525

CZ – Czech Republic, Klecany
Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst
Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup
Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid
Tel: +34 902 33 00 01
parker.spain@parker.com

FI – Finland, Vantaa
Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve
Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens
Tel: +30 210 933 6450
parker.greece@parker.com

HK – Hong Kong
Tel: +852 2428 8008

HU – Hungary, Budapest
Tel: +36 1 220 4155
parker.hungary@parker.com

IE – Ireland, Dublin
Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IN – India, Mumbai
Tel: +91 22 6513 7081-85

IT – Italy, Corsico (MI)
Tel: +39 02 45 19 21
parker.italy@parker.com

JP – Japan, Fujisawa
Tel: +(81) 4 6635 3050

KR – South Korea, Seoul
Tel: +82 2 559 0400

KZ – Kazakhstan, Almaty
Tel: +7 7272 505 800
parker.easteurope@parker.com

LV – Latvia, Riga
Tel: +371 6 745 2601
parker.latvia@parker.com

MX – Mexico, Apodaca
Tel: +52 81 8156 6000

MY – Malaysia, Subang Jaya
Tel: +60 3 5638 1476

NL – The Netherlands, Oldenzaal
Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Ski
Tel: +47 64 91 10 00
parker.norway@parker.com

NZ – New Zealand, Mt Wellington
Tel: +64 9 574 1744

PL – Poland, Warsaw
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal, Leca da Palmeira
Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest
Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow
Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga
Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SG – Singapore
Tel: +65 6887 6300

SK – Slovakia, Banská Bystrica
Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto
Tel: +386 7 337 6650
parker.slovenia@parker.com

TH – Thailand, Bangkok
Tel: +662 717 8140

TR – Turkey, Istanbul
Tel: +90 216 4997081
parker.turkey@parker.com

TW – Taiwan, Taipei
Tel: +886 2 2298 8987

UA – Ukraine, Kiev
Tel: +380 44 494 2731
parker.ukraine@parker.com

UK – United Kingdom, Warwick
Tel: +44 (0)1926 317 878
parker.uk@parker.com

US – USA, Cleveland
Tel: +1 216 896 3000

VE – Venezuela, Caracas
Tel: +58 212 238 5422

ZA – South Africa, Kempton Park
Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

European Product Information Centre
Freephone: 00 800 27 27 5374
(from AT, BE, CH, CZ, DE, EE, ES, FI, FR, IE, IT, PT, SE, SK, UK)



Parker Hannifin Ltd
Tachbrook Park Drive
Tachbrook Park, Warwick CV34 6TU
United Kingdom
Tel: +44 (0) 1926 317 878
CMC: parker.uk@parker.com
www.parker.com/hfde