



PARKER LEGRIS

LIQUIfit®

A Single Product Range for all Liquid Applications




LIQUIFIT® FOR COOLING APPLICATIONS



FREQUENCY CONVERTERS



DATA CENTERS




PLASTIC MOLDING



POWER CONVERSION




ENERGY STORAGE



ROBOTIC WELDING



LASER PROCESSING



SEMICONDUCTORS

MARKET CHALLENGES

- Reach the best thermal efficiency
- Optimize the design of the liquid cooling circuits
- Ensure the durability of the machine
- Improve productivity
- Simplify the maintenance of the machine

FLUID CONVEYANCE

Water, Glycol and many other coolants.

For such applications, we recommend you contact us to evaluate the fluid compatibility.



PRODUCT FEATURES

FAST & EASY

- Quick connection, no tool needed
- Automatic sealing and gripping

COMPACT & FLEXIBLE

- Numerous configurations offering high flexible installations solutions
- Space saving with cartridge systems

SMART & EFFICIENT

- Unrestricted design for maximal flow
- Flat sealing coupling system

SAFE & RESISTANT

- Push-in fittings 100% leak tested and individually dated in production
- Proven automated process which is camera controlled
- Robust test protocols are applied: ageing, endurance and mechanical tests such as vibrations, shock or burst pressure
- Large material compatibility



PRODUCT RANGES

LIQUIfit® Push-In Fittings



- Dimensions: 4 mm to 16 mm
- Working Pressure: up to 16 bar
- Working Temperature: -10°C to +95°C



LIQUIfit® Push-In Fittings with Metal Adaptor



- Dimensions: 4 mm to 16 mm
- Working Pressure: up to 16 bar
- Working Temperature: -10°C to +95°C
- 2 adaptor materials: stainless steel or nickel-plated brass



LIQUIfit® Push-In Fittings Full Metal



- Dimensions: 4 mm to 16 mm
- Working Pressure: up to 16 bar
- Working Temperature: -10°C to +130°C



Advanced PE Tubing



- Dimensions: 4 mm to 16 mm
- Working Pressure: up to 16 bar
- Working Temperature: -20°C to +95°C



Carstick+ Push-In Cartridges



- Dimensions: 4 mm and 6 mm
- Working Pressure: up to 16 bar
- Working Temperature: -40°C to +140°C




Carstick Push-In Cartridges



- Dimensions: 4 mm to 12 mm
- Working Pressure: up to 16 bar
- Working Temperature: -40°C to +95°C



LIQUIFIT® FOR DRINKING DISPENSERS & WATER TREATEMENT



WATER DISPENSERS



HOT & COLD DRINK DISPENSERS



FILTERS



INDUSTRIAL SOFTENERS



REVERSE OSMOSE



DESALINISATION



DENTAL CHAIRS

MARKET CHALLENGES

- Users' health protection
- Efficiency of connection systems

FLUID CONVEYANCE

Water, industrial water, beverages and steam.

For other fluids, please consult us.



REGULATIONS



NSF/ANSI 51



REACH ✓

For the most up-to-date and comprehensive information, please refer to the certificates on parker.com and/or www.nsf.org.

PRODUCT FEATURES

SPECIALLY DESIGNED FOR LIQUIDS

- EPDM seal for water and beverage conveyance
- FKM for more demanding media (i.e: steam)

SAFE FOR USERS' PROTECTION

- Bisphenol & phthalate free
- No raw material migration for the perfect fluid integrity with our bio-sourced engineered polymer

RELIABLE FOR PEACE OF MIND

- Compliant with the most demanding food & beverage regulations
- High sealing performance with the lowest pumping effect on the market (0,2mm only)
- Compact product: 20 to 40% more compact than competitors
- Proven automated process which is camera controlled
- 100% leak tested and individually dated in production

ROBUST FOR DEMANDING APPLICATIONS

- High resistance to aggressive environment with the 316L stainless steel adaptor, recommended for and beverage industry
- Nickel-plated version offers for industrial fluid applications

PRODUCT RANGES

LIQUIfit® Push-In Fittings



- Dimensions: 4 mm to 12 mm
- Working Pressure: up to 16 bar
- Working Temperature: -10°C to +95°C



LIQUIfit® Push-In Fittings with Metal Adaptor



- Dimensions: 4 mm to 12 mm
- Working Pressure: up to 16 bar
- Working Temperature: -10°C to +95°C
- 2 adaptor materials: stainless steel or nickel-plated brass



LIQUIfit® Push-In Fittings Full Metal



- Dimensions: 4 mm to 12 mm
- Working Pressure: up to 16 bar
- Working Temperature: -10°C to +130°C



Advanced PE Tubing



- Dimensions: 4 mm to 12 mm
- Working Pressure: up to 16 bar
- Working Temperature: -20°C to +95°C



Carstick+ Push-In Cartridges



- Dimensions: 4 mm and 6 mm
- Working Pressure: up to 16 bar
- Working Temperature: -20°C to +140°C



Carstick Push-In Cartridges



- Dimensions: 4 mm to 12 mm
- Working Pressure: up to 16 bar
- Working Temperature: -20°C to +95°C



LIQUIfit® Polymer Ball Valves



- Dimensions: 6 mm to 12 mm
- Working Pressure: up to 10 bar
- Working Temperature: 0°C to +65°C



LIQUIfit® Non-Return Valves



- Dimensions: 6 mm and 12 mm
- Working Pressure: up to 10 bar
- Working Temperature: 0°C to +65°C



LIQUIfit® OFFER OVERVIEW

Polymer Stud Fittings

Straight

6505
BSPT/ NPTF



6315
BSPT/ NPTF



6352
BSPP



6325
UNS



6521
BSPT/ NPTF



Elbows

6579
BSPT/ NPTF



6509
BSPT/ NPTF



Tees

6508
BSPT/ NPTF



6503
BSPT



Plugs

6355
BSPT



Tube-to-Tube Fittings

Straight

6306



Elbow

6302



Tee

6304



Y

6340



Cross

6307



Bulkhead Connector

Straight

6316



Plug-In Fittings

Elbows

6382



6380



Tees

6383



6388



Accessories

Plug-in

6366



6368



6326



6322



6351



Stud Fittings with Stainless steel adaptors

Elbows

6959
BSPP & Metric



6989
BSPP



6979
BSPT



Stud Fittings with Nickel-Plated Brass Adaptors

Elbows

6999
BSPP & Metric



6909
BSPT



Stud Fittings in Stainless Steel

Straight

6911
BSPP & Metric



6975
BSPT



6974
BSPP



Stud Fittings in Nickel-Plated Brass

Straight

6901
BSPP & Metric



6905
BSPT



6976



Cartridges

Carstick®

6300



Carstick+

6300



Flexible Calibrated Tubing

Advanced PE



1015Y..F
1030Y..F
1075Y..F
1096Y..F
1098Y..F

LIQUIfit® Related Products

3130



3110



0605



3000 71 00



LIQUIfit® Non-Return Valves

Non-Return Valves

7992



LIQUIfit® Ball Valves

In-Line

4020
2/2



4021
2/2



4023
2/2



Right-Angled

4022
2/2



4024
2/2





