



Parker Hannifin Corporation  
Parflex Division  
North Freedom Street  
Ravenna, OH 44266  
Office 330 296 2871

**Subject: Manufacturer's Declaration (PED)**

**Date: October 9, 2025**

Issued in accordance with the Pressure Equipment Directive (2014/68/EU)

**Name and Address of Manufacturer:**

Parker Hannifin Corporation, Parflex Division, USA

1300 North Freedom Street, Ravenna, OH. 44266

1717 Dufek Drive, Manitowoc WI. 54220

11151 Cash Road, Stafford TX. 77477

4700 Lone Star Blvd. Ft Worth TX. 76106

700 South 4th Ave. Mansfield TX. 76003

**Description of Pressure Equipment:**

Thermoplastic, elastomeric, fluoropolymer and metallic tubing and reinforced hose having internal diameters not greater than DN25, as covered by Article 4 of the Directive and not used as safety equipment as defined in Article 2 of the Directive. Metal tubing and plastic tubing bundles with individual tubes not greater than DN25, as covered by Article 4 of the Directive and not used as safety equipment as defined in Article 2 of the Directive. The applicable products as listed in on page 2 of this declaration are manufactured in accordance with ISO9001 or AS9100D Quality Systems following appropriate national and international standards, this being recognized as sound engineering practice.

**Name and Address of the Notified Body Monitoring the Manufacturer's Quality Assurance System:**

Bureau Veritas North America Inc., New York, NY 10018:

- Certificate No. EMS811130 (ISO14001:2015)
- Certificate No. FM805447 (ISO9001:2015) Manitowoc, WI
- Certificate No. FM818644 (ISO9001:2015) Stafford, TX
- Certificate No. FM799526 (ISO9001:2015) Ravenna, OH
- Certificate No. US796795 (ISO9001:2015) Ft Worth and Mansfield, TX

**Standard Parflex products do not fall into this directive and do not require CE marking:**

- for liquids of group 2 when  $DN \leq 200$  and  $PS \leq 500$  bar (Definition: hoses and tubing less than 7-7/8 inch ID with a working pressure less than 7250 psi are exempt under Article 4.
- for gases of group 2 when  $DN \leq 100$  and  $PS \times DN \leq 3500$  (Definition: hoses and tubing less than 3.9 inch ID with pressure x size less than or equal to 2000 psi - inch (3500 bar - mm) are exempt under Article 4
- for gases of group 1 (flammable and dangerous) when  $DN \leq 25$  (Definition: hoses and piping 1 inch ID and smaller are exempted under Article 4.



Parker Hannifin Corporation  
 Parflex Division  
 North Freedom Street  
 Ravenna, OH 44266  
 Office 330 296 2871

#### Manufacturers Declaration

Issued in accordance with the Pressure Equipment Directive (2014/68/EU)

| Product Type                                                               | Product Series                                                                                                                                                                                                                                                                                                                                                                                                 | Applicable Sizes               | Material      |
|----------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|---------------|
| Metal Instrumentation Tubing Bundles                                       | MJ, MA, MAJ & MJR, TT, SL, SH, TL, TH, CL and CH Series                                                                                                                                                                                                                                                                                                                                                        | All tube sizes under DN25 (1") | All Materials |
| Plastic Instrumentation Tubing Bundles                                     | PJ, PA & PAJ Series                                                                                                                                                                                                                                                                                                                                                                                            | All tube sizes under DN25 (1") | All Materials |
| Thermoplastic Hydraulic, Pneumatic, Ultra High Pressure and Fuel Hoses     | 510R, 518D, 510D, 520N, 528N, 527BA, 53DM, 538DM, 53LT, 538LT, 540P, 55LT, 560TJ, 563TJ, 563LT, 56DH, 575X, 575XN, 578X, 580N, 588N, 590TJ, 594TJ, 83FR, 1035HT, HLBD, MSH, MSXL, PTH, S5N, S6, S9, 5CNG, CNGRP, 2020N, 2022N, 2390N, 2240D, 2245D, 2245N, 2248D, 2340N, 2380N, 2388N, 2440D, 2448M, 2640M, 2240N, 2440N, 2448N, 2580N, 2640N, 2648N, 2240N, 2248N, 2580N, 2648N, HCRV, PFX Series             | All tube sizes under DN25 (1") | All Materials |
| Parflex and NyCoil Thermoplastic and Texloc Fluoropolymer Tubing           | E, EB, PEFR, HDPE, N, PAT, NR, NTNA, PP, PPB, U, UM, HU, HUM, PV, TFH, TFT, TFS, TFL, 101, 201, HS2T, HS4T, CV, CVH, CVL, 81914, TSWTF, 103, 203, HS1.3, HS1.6, HS1.25, CV, 81914, CR, 703, 104, 204, 104, 205, 704, 705, 110, 111, FEP, PTFE, PFA, HUFR, 101, 201, TFL, TFS, TFT, AWG, TFH, TSWTF, HS2, HS4, CONVO-TEX® CV03, CR03, 705, 104, 204, 105, 205, 110, PVDF, Nycoil® Nylon and Polyurethane Tubing | All tube sizes under DN25 (1") | All Materials |
| Parflex and Page Fluoropolymer Hoses, Metallic Hoses and Metallic Fittings | 919, 919B, 919J, 919BJ, 919U, 929, 929B, 929BJ, 939, 939B, 944B, 955B, STW, STB, SCW, SCB, NCW, NCB, 9A, 9M, 9P                                                                                                                                                                                                                                                                                                | All tube sizes under DN25 (1") | All Materials |
| Parflex and NyCoil NoMar and Fast-Stor Tubing Coils                        | Nycoil®, NoMar®, Fast-Stor Series®                                                                                                                                                                                                                                                                                                                                                                             | All tube sizes under DN25 (1") | All Materials |
| Thermoplastic Airbrake Tubing, BrakCoil, Harnesses and DEF Hose Assemblies | PFT, HTFL, 1120, BrakCoil®, SliderCoil™, SCR                                                                                                                                                                                                                                                                                                                                                                   | All tube sizes under DN25 (1") | All Materials |